

Breaker BQD 2P 15A 480V AC 14kA



Number of poles	2
Suitability for operation	CONSTRUCTION
Electricity	
Continuous current rated value	15 A
Supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
Ambient temperature during operation maximum	40 °C
Model	
Product brand name	SIEMENS
Special product feature	PANELBOARD MOUNT
Type of electrical connection	LOW TAB
Mechanical Design	
Depth [in]	4 in
Design of the overload release	THERMAL MAGNETIC TRIP UNIT
Design of the product	BQD
Height [in]	2 in
Material of the enclosure	MOLDED CASE CIRCUIT BREAKER
Size of the circuit-breaker	100A

Width [in]

3 in

General product approval

Standard

UL 489 CSA-C22.2 IEC 60947-2

last modified:

10/24/2018