

LC 60A 2 CKT INDOOR SURFACE60A 1PH ML LC MURRAY  
SIMILAR TO E0204ML1060S

General technical data	
Configuration of the busbars	60A
Mounting type	Surface
Phase number	1
Suitability for operation	Residential

Electricity	
Ampacity	60 A
Voltage between phase and Ground (GND) rated value	120 V
Voltage between phase and phase rated value	240 V

Switching capacity	
Switching capacity current acc. to EN 60898 rated value	22000 A

Model	
product brandname	Murray
Product sub brand name	Load Centers

Mechanical Design	
Number of width units for installation width	2
Size of the circuit-breaker	ML
Width [in]	925.592 in

**last modified:** 02/22/2017