

BREAKER BQD 2P 25A 480VAC 14KA



Number of poles	2
Suitability for operation	CONSTRUCTION
<b>Electricity</b>	
Continuous current rated value	25 A
Supply voltage frequency rated value 50/60 Hz	Yes
<b>Environmental conditions</b>	
Ambient temperature during operation maximum	40 °C
<b>Model</b>	
product brandname	SIEMENS
Special product feature	PANELBOARD MOUNT
Type of electrical connection	LOW TAB
<b>Mechanical Design</b>	
Depth [in]	4.1 in
Design of the overload release	THERMAL MAGNETIC TRIP UNIT
Design of the product	BQD
Height [in]	2.9 in
Material of the enclosure	MOLDED CASE CIRCUIT BREAKER
Size of the circuit-breaker	100A

Width [in]

2 in

General product approval

Standard

UL 489 CSA-C22.2 IEC 60947-2

**last modified:**

11/21/2017