



Description 1500W BT-56 Mogul Base
Ordering Code 49201
UNSPSC Code 39101614

Specifications

Watts	1500
Base Type	Mogul Screw (E39)
Bulb Type	BT56
MOL in/mm	15.5/393.7
MOD in/mm	7.09/180
LCL in/mm	9.50/241.0
Mercury Content (mg)	82.5
HG Form	liquid
Approx Initial Lumens	155000
Approx Mean Lumens	126000
CT deg K	4000
CRI	70
Rated Life	3,500
Common Code	MVR1500/U
ANSI Ballast	M48
Fixt Rqmt	Enclosed
Burning Position	Universal
Special Desc	Probe Start
Coating	Clear
Approvals	IMERC

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975
 Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335