



Shrink-Kon[®]

Thin-Wall Heat-Shrinkable Tubing

T&B Catalog Number:

UPC Number: CPO250-0-6
Status: 78621085166
Description: Active

Thin-Wall Heat-Shrinkable Tubing for Cable Range 16 - 10 AWG, Expanded Dia. 1/4, Length 6 in., rated for 600V, 125 degrees C, Material: Cross-linked polyolefin - Non-lined, Black

Features

Flame-retardant, cross-linked polyolefin.
 Meets UL 224, 125°C; CSA 22.2 No. 198.1, 125°C;
 MIL-DTL-23053/5 Class 1&2; AMS 3636 & 3637;
 DEF STAN 59-97, Issue 3, Type 2a

General

Style	CPO Series Non-Lined, 6 in. lengths
Color	Black
Temperature Range	-55°C - 135°C
Shrink Ratio	2:1

Dimension Information

Minimum Expanded I.D. (inches)	0.25
Maximum Recovered I.D. (inches)	0.125
Nominal Recovered Wall (inches)	0.025
Cable Range	16 - 10 AWG
Standard Length (inches)	6

Specifications

Shrink Temperature	120°C
--------------------	-------

Packaging

T&B Order Multiple	20
T&B Inner Pack	20
Package in Units	200
T&B Sold in UOM	Each
T&B Weight Per UOM	0.5 lbs. per 100

Application Support

MSDS Number	msds-0020-tb2
Specifications	Available on Website
Overview	Available on Website

Notes

Order multiple is standard package.
 Custom colors available. Contact Customer Service.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com