


mini-monty pendant

DESCRIPTION

Mouth-blown elliptical shaped Murano glass fused with millefiore glass and silver flakes. Includes (1) 50 watt low-voltage GY6.35 base Xenon bi-pin lamp or 8 watt replaceable 500 lumen 80 CRI 3000K LED SORAAA® module and 6' of field-cutable suspension cable. For use with 24 volt transformer, add suffix "-24" to item number (LED lamp option is not compatible with 24 volt transformers).



opal



blue mocha opal red

ORDERING INFORMATION

model	color	finish	lamp	mount
HS338	BU blue	BZ bronze	1B50 GY6.35 Xenon 50w	FSJ fusion jack
	MO mocha	SC satin nickel	1B50 GY6.35 Xenon 50w (T20)	MPT monopoint
	OP opal		LEDS830 LED module 8w 90 CRI 3000K (T20/T24)	MRL monorail
	RD red			

FSJ mount requires a Fusion Jack canopy, sold separately.
MPT mount includes 4" Round Flush Canopy.

FIXTURE TYPE: _____

JOB NAME: _____

NOTES: _____



7400 Linder Avenue
Skokie, Illinois 60077

T 847.626.6300
F 847.626.6350

www.lblighting.com



©2018 LBL Lighting. All Rights Reserved. The "LBL Lighting" graphic is a registered trademark of LBL Lighting. LBL Lighting reserves the right to change specifications for product improvements without notification.