

**Catalog Number:** TY5244MX  
**Product ID:** 7TCG009090R0005  
**UPC Number:** 78621087294  
**EAN Number:** 05414363065487  
**Status:** Active



Actual



Actual

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 368.3mm (14.5 Inches), Width of 3.61mm (0.142 Inches), Thickness of 1.31mm (0.052 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds)

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.
- Application Tools: ERG50, WT1-TB

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5037 Cable Ties & Wraps
Brand Name	Ty-Rap
Type	Standard
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Width	0.142 Inch/3.61mm
Length	14.5 Inches/368.3mm
Thickness	0.05 Inch/1.31mm
Bundle Diameter	0.08 Inch/2mm-4.09 Inches/102mm
Material	Nylon/Polyamide 6.6
Color	Black
Lock Mechanism	Stainless Steel Barb
Tensile Strength	40 Pounds/180 Newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	3.61mm
Length belt/tape/tie	368.3mm
Tie thickness	1.31mm
Max. bundle diameter	102mm
Min. holding force	180N
Model	Internal toothing
Band closure	Steel nose
Halogen free	Y

### Packaging

Inner Quantity	100
Outer Quantity	500

Outer Dimensions (inches)	16.3x6.9x4.5
Weight Uom	10 lbs. per 1000

## Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com