



Actual

Catalog Number: RC10-250A
Product ID: 7TAI029690R0014
UPC Number: 78621089447
EAN Number: 05414363159117
Status: Active

Nylon Insulated Open Top 90 Degree Flag Female Disconnect Terminal, Length .80 Inch, Width .88 Inch, Maximum Insulation .245, Tab Size .250x.032, Wire Range #12-#10 AWG, Color Yellow, Brass, Tin Plated

- Unique construction of the female disconnect offers long-term dependability.
- Brazed seam serrated barrel provides maximum tensile strength.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RC2577F

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.
Standard	UL E66716
Material	Brass
Finish	Electro -Tin Plated
Color	Yellow
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Yellow
Material insulation	PA
Material	Brass

Packaging

Inner Quantity	50
Inner Dimensions (inches)	2.5x1.3x3.5
Outer Quantity	250
Outer Dimensions (inches)	12.1x10.5x7.9
Weight Uom	6.88 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com