




DIMENSIONS:

48"(L) x 4-7/8"(W) x 3-7/8"(H)



LSL-4FT-40W-50K-D LSL-4FT-40W-40K-D LSL-4FT-40W-35K-D

LED SHOP LIGHT WITH ADJUSTABLE SUSPENSION CABLE

Ideal for a variety of industrial, commercial and residential applications. Surface mount, wall mount or suspension mounting available.

ELECTRICAL SPECIFICATIONS:

- Voltage: 120-277VAC 50/60Hz
- Wattage: 40W
- Power factor: >0.9
- Efficacy: 110LM/W

HOUSING SPECIFICATIONS:

- Evenly illuminated Frosted White polycarbonate lens
- Operating temperature: -22°F~104°F
- Lifespan: 50000 Hrs.
- IP rating: Dry Locations

CERTIFICATIONS: ETL, DLC




MODEL	WATTS	VOLTAGE	LUMENS	COLOR TEMP
LSL-4FT-40W-50K-D	40W	120~277V AC	4193lm	5000K
LSL-4FT-40W-40K-D	40W	120~277V AC	4070lm	4000K
LSL-4FT-40W-35K-D	40W	120~277V AC	4070lm	3500K

LIGHTING SPECIFICATIONS:

- Total lumens: 4070lm and 4193lm
- Color temperature: 3500K, 4000K and 5000K
- Color rendering index: >82

WARRANTY: 5 years



Height	Average Lux (lx)	Light range (dia.)
1M	281.7	323.2cm
2M	70.43	646.4cm
3M	31.3	969.6cm
4M	17.61	1292.8cm
5M	11.27	1616.0cm

