



Actual

Catalog Number: TY15X2WPG6
Product ID: 7TAA104030R0032
UPC Number: 78621095650
Status: Obsolete
Replacement Catalog: TYD15X2WPG6

Wiring Duct Wide Slot 1-1/2 Inch X 2 Inch Rigid PVC Gray

- Wide fingers and slots increase rigidity and enable insertion of bundles.
- V-Shaped slot lead-in enables easier and faster wire installation.
- Rounded edges keep hands and wires free of abrasion.
- Non-slip cover does not slide easily and resists vibration.
- Flush cover attaches flush with sidewall for finished look.
- Dual score lines are designed to yield clean breakoffs at the base of the slot and the duct.
- Versatile North American and DIN Standard mounding holes enables same duct for multiple applications.

North American Specifications (UNSPSC)

UNSPSC	39131712 Wiring duct
IGCC	5580 Wiring duct
Brand Name	Ty-Duct
Type	Wiring Duct
Special Features	Wide fingers and slots increase rigidity and enable insertion of bundles. V-Shaped slot lead-in enables easier and faster wire installation. Rounded edges keep hands and wires free of abrasion.
Width	1.75
Depth	2.10
Length	6
Mounting Holes	Yes
Material	Rigid PVC
Color	Gray

European Specifications (ETIM)

ETIM	EC000012 Slotted cable trunking system
Height	53.3mm
Width	44.5mm
Length	1829mm
Halogen free	Y
Type of fastening	Adhesive film
With cover	N
Colour	Light grey

Packaging

Inner Quantity	6
Outer Quantity	120
Outer Dimensions (inches)	73x9.5x6.5
Weight Uom	23.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000180

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com