




Actual



Representative

**Catalog Number:** ARL-2  
**Product ID:** 7TAA118240R0001  
**UPC Number:** 04226932115  
**Status:** Active

3/4 inch Threaded Die Cast Aluminum Conduit Body with Left/Right Side Opening. For Use with Rigid/IMC Conduit.

- Retained stainless steel cover screws
- Smooth throats for easy wire pulling
- Spacious, accessible wiring chamber provides a convenient location to pull conductors and make splices.
- For use with rigid/IMC conduit
- Threaded conduit bodies maintain a weather resistant conduit system when used with covers and gaskets.

### Header

3D Model Available on Website

### North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Brand Name	Red Dot
Type	Conduit Body - Series A - Rigid/IMC
Special Features	Retained Stainless Steel Cover Screws
Application	For Use with Rigid/IMC Conduit
Standard	UL E28688, CSA
Hub Size	3/4 Inch
Material	Aluminum Die Cast

### Packaging

Inner Quantity	10
Inner Dimensions (inches)	10x6.81x3.06
Outer Quantity	50
Outer Dimensions (inches)	20.4x8.7x7.7
Weight Uom	0.52 lbs. Each

### Documents / Support Tools

Technical Data Sheet US Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)