



Actual

**Catalog Number:** K822BR  
**Product ID:** 7TAA002680R0003  
**UPC Number:** 04226968150  
**Status:** Active

Path Light, Height 7-1/2 Inch or 10 Inches, Width 4-1/4 Inches, 13 Inch x 2 Inch Schedule 40 PVC Mounting Tube, Bronze, Die Cast Zinc, A15 40 Watt Maximum 120V Medium Base Lamp, Extension Sleeve Included

- Sturdy die-cast aluminum construction provides durability
- Architectural bronze color blends into landscape and deck areas
- Aluminum mounting tube cap houses and protects wire connection (ground installed fixtures)
- PVC ground tube provides an innovative installation method saving costly labor and traditional installation materials (ground installed fixtures)
- Wire connectors and ground wire enable safe, easy power connections
- Fixtures use regular household voltage, 120V.
- Easy to install, only three wire connections per fixture are required
- No need to pour concrete, all connections are made above ground.

### North American Specifications (UNSPSC)

UNSPSC	39111605 Landscape lighting
IGCC	3908 Landscape lighting
Brand Name	Red Dot
Type	Landscape Lights
Special Features	Copper-free aluminum construction provides increased corrosion resistance
Application	Low maintenance indoor/outdoor lighting where moisture, dirt, dust, corrosion and rough service are problems.
Standard	UL E51152
Wattage	40
Voltage Rating	120
Number Of Lamps	1
Fixture Material	Die Cast Zinc
Color	Bronze
Socket Type	Porcelain, Center Contact, Brass Screw Shell, Medium Base
Width	4-1/4 Inches
Height	7-1/2 Inches

### Packaging

Outer Quantity	4
Outer Dimensions (inches)	20.1x9.8x15.1
Weight Uom	2.84 lbs. Each

### Documents / Support Tools

SDS US 1	sds-00029-tb2
Technical Data Sheet US	Available on Website
Instruction Sheet 1	ta03949-tb2
Catalog US 1	Available on Website

**For further technical assistance, please contact us...**

Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

8155 T&B Blvd.  
Memphis, TN 38125

Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)