



Actual

**Catalog Number:** 4070-9502  
**Product ID:** 7TAA040420R0012  
**UPC Number:** 78635850610  
**Status:** Obsolete  
**Replacement Catalog:** 4070-95

Round Ceiling/Fixture Outlet Box with Bar Hanger, Volume 20.8 Inches, Diameter 4 Inches, Depth 2-3/8 Inches, Color Brown, Material Phenolic, Mounting Mean 24 Inch Bar Hanger Adjustable 16-1/2 Inch Maximum - 27 Inch Minimum, with #36 Clamps

- #36 clamps bulk packed

### North American Specifications (UNSPSC)

UNSPSC	39121316 Ceiling box
IGCC	4448 Ceiling box
Brand Name	Carlton
Type	Ceiling Boxes
Special Features	#36 clamps bulk packed
Application	Suitable for fixture support up to 50 lbs.
Standard	UL e11461
Material	Non-Metallic
Color	Brown
Mounting	24 Inch Adjustable bar hanger
Cubic Capacity	20.8
Knockouts	No

### European Specifications (ETIM)

ETIM	EC002601 Box/housing for built-in mounting in the wall/ceiling
Mounting method	Other
Shape	Round
Construction type	Device connection box (round/square)
Equipped with	Support rail
Diameter	101.6mm
Depth	-mm
Mounting switching equipment	Screwing
Pipe locking	N
Pipe locking optional	N
Surface protection	Other
Cover	None
Cover attachment	Not applicable

### Packaging

Outer Quantity	50
Outer Dimensions (inches)	26x19x10.75
Weight Uom	75 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)