

General Information

Extended Product Type:	OT200U03
Product ID:	1SCA022723R0220
EAN:	6417019232645
Catalog Description:	OT200U03 Non-fusible disconnect switch
Long Description:	Handle and shaft must be ordered separately.

Categories

Products » Low Voltage Products and Systems » Switches » Switch Disconnectors

Ordering

EAN:	6417019232645
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365080

Dimensions

Product Net Width:	170 mm
Product Net Height:	170 mm
Product Net Depth:	70 mm
Product Net Weight:	1.577 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	183 mm
Package Level 1 Height:	95 mm
Package Level 1 Length:	240 mm
Package Level 1 Gross Weight:	1.577 kg
Package Level 1 EAN:	6417019232645

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q4
--------------	---

Additional Information

Earthing Switch Type:	No Additional Type
Handle Type:	None
IIT Publishing Status:	Level 0 - Information enabled
Includes:	None
Mounting Type:	Normal
Number of Poles:	3
Operating Mechanism:	Mechanism at the end of the switch
Operating Mode:	Front Operated
Pollution Degree:	3
Power Loss:	6.5 W
Product Main Type:	OT200U
Product Name:	Switch-disconnector
Rated Impulse Withstand Voltage (U _{imp}):	12 kV
Rated Insulation Voltage (U _i):	1000 V
Rated Operational Current AC-22A (I _e):	(380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Current AC-23A (I _e):	(380 ... 415 V) 250 A (500 V) 250 A (690 V) 250 A
Rated Operational Voltage:	1000 V
Rated Short-time Withstand Current (I _{cw}):	for 1 s 8 kiloampere rms
Special Functions:	No
Standards:	IEC&UL
Terminal Type:	Lug terminals

Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	1SCC301001C0201
Declaration of Conformity - CE:	1SCC301137D0202

Classifications

ETIM 5.0: EC000216 - Switch disconnector

Object Classification Code: Q

