

# CS6360C

50Amp, 125V AC, Non-NEMA, 2P, 3W, Black & White Locking Connector, Industrial Grade, Grounding, California-Style(CS) – BLACK-WHITE



UPC Code : 07847732601

Country Of Origin : Mexico



Leviton's Industrial Grade Locking Devices are built to provide unparalleled quality and superior performance in the most severe industrial settings. Leviton combines the best materials available with superior production standards to produce a broad selection of Locking Devices of unmatched flexibility and dependability.

## Technical Information

### Electrical Specifications

**Amperage** : 50 A

**Current Interrupting** : Certified for current interrupting at full rated current

**Dielectric Voltage Withstand** : 2000V minimum per UL 498

**Grounding** : Grounding

**Maximum Working Voltage** : 125V as rated

**Pole** : 2

**Temperature Rise** : Max 30°C temp rise at full-rated current after 150 cycles of OL at 150% rated DC current

**Voltage** : 125 VAC

**Wire** : 3

### Environmental Specifications

**Environment** : Dry

**Flammability** : Rated HB or better UL94

### Material Specifications

**Assembly Screws** : Brass

**Cable Clamp Screw** : Phillips Head, SS 304

**Color** : Black-White

**Dust Shield** : Santoprene TPE

**Face Module** : Nylon

**Ground Post** : Brass

**Ground Shunt** : Bronze

**Housing Material** : Nylon

**Plug Blade** : 0.1000inch thick Brass

**Plug Blade Shroud** : SS 302/304

**Standard Cable Clamp** : Nylon

**Terminal Block** : 0.062inch thick Copper

**Terminal Set Screw** : SS 302/304

**Wiring Chamber** : Nylon

### Mechanical Specifications

**Cord Range** : .680 - 1.125

**Product ID** : Ratings and Catalogue No. molded into face and stamped into shroud

**Terminal ID** : X, W, Y, Z and Green for ground

### Product Features

**Brand** : Black and White

**Color** : Black-White

**Device Type** : Locking Connector

**NEMA** : Non-NEMA

### Standards and Certifications



**CSA C22.2 No. 42** : File 152105

**NOM** : 057

**RoHS** : Compliant

**UL 498** : File E13399

**Warranty** : Lifetime Limited



## SPECIFICATION SUBMITTAL

JOB NAME: <input type="text"/>	CATALOG NUMBERS: <input type="text"/>	
JOB NUMBER: <input type="text"/>	<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

**Visit our Website at: [www.leviton.com](http://www.leviton.com)**

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

