

JOB NAME: \_\_\_\_\_

DATE: \_\_\_\_\_

TYPE: \_\_\_\_\_



### DIMENSIONS:

13"(H) x 6"(D)

### ACCESSORIES INCLUDED:



Silicon-filled  
Wire Nuts



5' SJTW 20AWG Lead  
Wire



8-1/2"  
Non-metallic Spike



LED Tower

## AA-146-BZ AA-146-BK

### 12V LED PAGODA LIGHTS

Ideal for Landscape light, illuminating a path, highlighting garden area, highlighting uneven terrain.

#### ELECTRICAL SPECIFICATIONS:

- Voltage: 12VAC/DC
- Wattage: 3W
- Efficacy: 66LM/W

#### HOUSING SPECIFICATIONS:

- Solid Brass—Antique Bronze Finish (BZ), Black (BK)
- Silicon-filled Wire Nuts
- 5" SJTW 20AWG Lead Wire
- 8-1/2" Non-metallic Spike
- IP Rating: IP67

#### CERTIFICATIONS:



MODEL	WATTS	VOLTAGE	LUMENS	COLOR TEMP
AA-146-BZ	3W	12VAC/DC	200LM	3000K
AA-146-BK	3W	12VAC/DC	200LM	3000K



Pagoda Lights  
Replacement Glass  
(Not Included)

MODEL	DESCRIPTION
AA-146-RG	Pagoda Lights Replacement Glass (Not Included)

#### LIGHTING SPECIFICATIONS:

- Lens: Heavy-Duty Clear Glass Lens
- Light Source: Integrated SMD LED Tower
- Total lumens: 200LM
- Color temperature: 3000K
- Beam angle: 360°

#### WARRANTY: 3 years

