



16" Color preference® Flushmount

1600lms | 120-277VAC | Model 54437511 | Part FM-16-24-902-MV-D-B

- > Energy Saving 24 Watt Integrated LED
- > Uses 76% Less Energy than Equivalent 100 Watt Incandescent Bulb
- > Soft White 3000k CCT
Cool White 4000k CCT
Daylight 5000k CCT
- > Lasts 45 years or 50,000 Hours Continuous Use
- > Maintenance Free — No Bulb Replacements
- > 5 Year Limited Warranty



SPECIFICATIONS

Model	54437511
Part	FM-16-24-902-MV-D-B
Description	16" Color preference® Flushmount-Dimmable
Input Voltage (VAC)	120-277
Wattage	24
Dimmability	0-10V
Average Rated Life¹	50,000 hours
Typical Lumens²	1600
CCT³	3000k/4000k/5000k
Location Rating	UL Damp
CRI⁴	90
Beam Angle	120
Operating Temperature	Min -4°F (-20° C), Max 95°F (35° C)
Power Factor	>0.9
R9	59
DUV	0.00039
CBCP	389
Operating Frequency (Hz)	50/60

1 Hours lifetime with 70% lumen maintenance
 2 Thermally stable typical lumens (±10%)
 3 Thermally stable CCT (±10%)
 4 Color rendering index/Ra

TO ORDER:
www.ETiSSL.com
 Call: 1.855.ETi.SSLI
 1.855.384.7754


ETI

LED lighting facts
A Program of the U.S. DOE

Light Output (Lumens)	1600
Watts	24
Lumens per Watt (Efficacy)	66.67

Color Accuracy Color Rendering Index (CRI)	90
--	-----------

Light Color Correlated Color Temperature (CCT)	3000 (Bright White)
--	----------------------------



All results are according to IESNA LM-79-2008: Approved Method for the Electrical and Photometric Testing of Solid-State Lighting. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the Label Reference Guide.

Registration Number: 5BAM-6U7WDI (Revised 8/11/2017)
 Model Number: 544375##(11-30)
 Type: Luminaire - Other





16" Color preference[®] Flushmount

1600lms | 120-277VAC | Model 54437511 | Part FM-16-24-902-MV-D-B

SHIPPING INFORMATION

Model	54437511
Part	FM-16-24-902-MV-D-B
UPC	849489006512
Product Dimensions (L x W x H in.)	15.28 x 15.28 x 2.99
Product Dimensions (L x W x H cm.)	38.8 x 38.8 x 7.6
Product Weight (lbs.)	2.08
Inner Carton Quantity	N/A
Inner Carton Bar Code	N/A
Inner Carton Dimensions (L x W x H in.)	N/A
Inner Carton Dimensions (L x W x H cm.)	N/A
Inner Carton Weight (lbs)	N/A
Master Carton Quantity	4
Master Carton Bar Code	50849489006517
Master Carton Dimensions (L x W x H in.)	17.2 x 13.7 x 17.3
Master Carton Dimensions (L x W x H cm.)	43.7 x 34.8 x 44.0
Master Carton Weight (lbs)	13
Pallet Quantity	72

COMPATIBILITY

Dimmers:

S/N	Dimmer Brand	Dimmer Model#
1	Lutron	NTSTV-DV-WH
2	Lutron	DVSTV-WH
3	Lutron	DVTV-WH
4	Lutron	NFTV
5	Leviton	IPL06-1OZ

Motion Sensor:

Model 90600145

AVAILABLE ACCESSORIES

Model	Description
95443751102	Diffuser Lens

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, Please see www.etissl.com/fcc15b

TO ORDER:
www.ETiSSL.com
Call: 1.855.ETi.SSLI
1.855.384.7754

ETi Solid State Lighting, Inc.
720 Corporate Woods Parkway
Vernon Hills, IL 60061
Phone: 855.384.7754
Fax: 847.383.6256