

WB1901PN: 2 - Light Wall Sconce



Dimensions:

Width:	5"	Extends:	5 3/8"
Height:	17 3/8"	Wire:	8"
Weight:	3 lbs.	Mounting Proc.:	Wall / Bath
		Connection:	Mounted To Box

Bulbs:

2 - Candelabra Torpedo 60w Max. 120v - Not included

Material List:

1 Body - Steel - Polished Nickel

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (WB1901)

Collection: Bryan

Arms have 120° range of motion for positioning light where you need it.

UPC #: 014817579994

Finish: Polished Nickel (PN)

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate			3/4	5	11 1/2	

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	WB1901PN	1	014817579994	20	8.25	8.25	0.788	3.5	175	Yes
NJ Pallet		96		48	40	72	80	336		No
NV Pallet		96		48	40	72	80	336		No