



# S9963

5.5W CFC/LED/30K/CL/120V  
 5.5 watt CA11 LED; Clear; Candelabra base; 3000K; 500 lumens; 120 volts

## Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures



S9963

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9963	045923099632	120	5.5	60W	CA11	Candelabra	E12

  

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
5.5W CFC/LED/30K/CL/120V	Dimmable	<a href="#">Compatible dimmers for S9963</a>	Clear	3 7/8"	1-3/8"	500	15000

  

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR
3000	Soft White	80	360	-20C (-4F) to a maximum of +45C (+113F)	24	Box	ENERGY STAR

  

CEC Status	RoHS Compliant	Fixture Type	UL or ETL Listed	UL Classification	Warranty
Non-Compliant <a href="#">Possible sub: S8552</a>	Yes	Enclosed Rated	Yes	cULus - Damp Location Rated	<a href="#">3 Year Limited</a>



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

