



GE  
Lighting

**65390 - GE LED R30**

**LED12DBR30/830**

Energy-efficient LED lamps. Long life.

**Product Photo**



**GENERAL CHARACTERISTICS**

Base Description	Medium Screw
Base Type	Screw-In
Lamp Type	LED-BR
Primary Application	Indoor Floodlight
Product Color	Silver
Product Technology	LED
Rated Life (Hours)	50000 h
10 Digit U	4316865390
Lamp Count	1
Life in Years	45.7 yr
Estimated Energy Cost per Year	1.45
Base	E26
Bulb Shape	BR30

**PHOTOMETRIC CHARACTERISTICS**

Lumens per Watt (Efficacy)	63 lm
Nominal Initial Lumen per Watt	63
Initial Lumens-nominal	750 lm
Color Rendering Index-CRI	83
Color Temperature	3000 K

**PRODUCT INFORMATION**

Product Code	65390
Description	LED12DBR30/830
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168653909
Standard Package GTIN	10043168653906
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168653909
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168653909
Standard Package GTIN	00043168653909
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168653909

**ELECTRICAL CHARACTERISTICS**

Voltage <Nom>	120 V
Rated power (Watts)	12 W