



Representative Image

Catalog No. TC35362

Description: 60A 3P DBL THR N1 600V NONFUSE

UPC No 783164001754

Home > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Double Throw

Designed for commercial and industrial applications where safety, high performance and continuity of service are essential. Listed to UL standard 98 enclosed and dead front switches. Suitable for use as service equipment when installed in accordance with the National Electrical Code. Suitable for use as transfer equipment in standby systems in accordance with Article 702 of the National Electrical Code. Fusible and non-fusible switches available (consult BuyLog for interrupt ratings). 60/75 C conductor rating. Full cover interlocks. TC351754

Descriptors

Category	Disconnect & Safety Switches
GO Schedule	SB

Specifications

Voltage	600 AC
Amperage	60 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 1 (Indoor)
Options	None
Wire Range (Cu/Al)	14-4 (Cu)
240 Vac, NEC Std, 3-ph	10.0 hp
480 Vac, NEC Std, 3-ph	10.0 hp
600 Vac, NEC Std, 3-ph	10.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	No
UL Listed	Yes

Dimensions

Height	18.8 in
Depth	6.3 in
Width	11.4 in
Weight	21.0 lb

Publications

Title	Publication No.	Publication Type
60A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH115	Drawings-Outline and Dimensional
Double-Throw Safety Switch, NEMA 3R 2 pages, 30-400 Ampere Double-Throw Safety Switch	DEH-44154	Installation and Instruction

Additional Documentation: Visit our Publication Library to find technical documentation, time current curves, CSI Specifications and promotional literature.