



GE
Lighting

90602 - GE HIR™ PLUS PAR38

67PAR/HIR+/FL25

☞ Up to 42% more efficient than standard halogen

☞ Up to 27% energy savings

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Skirt
Base Type	Screw-In
Filament	CC-8
Life in Years	3.8 yr
Rated Life Hours-nominal	4200 h
Primary Application	Indoor and outdoor Floodlight
Product Technology	Halogen
Base	E26/50x39
Bulb Shape	PAR38

PHOTOMETRIC CHARACTERISTICS

Beam Spread	25 deg
Center Beam Candle Pwr Candela	5000 cd
Nominal Initial Lumen per Watt	22
Initial Lumens-nominal	1500 lm
Color Temperature	2800 K

PRODUCT INFORMATION

Product Code	90602
Description	67PAR/HIR+/FL25
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168906029
Standard Package GTIN	10043168906026
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168906029
Alternative Unit Of Measure	EACH
Standard Package Quantity	12
Ean UPC	043168906029
Standard Package GTIN	00043168906029
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	12
Sales Unit	Each
UCC	043168906029

DIMENSIONS

Diameter	4.75 in
----------	---------

ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per Year	8.07 \$
Input Voltage [nom]	120 V
Rated power (Watts)	67 W

CAUTIONS & WARNINGS

Caution

Lamp may shatter and cause injury if broken

Do not use lamp if outer glass is scratched or broken.

Risk of Burn

Allow lamp to cool before handling.

Warning

Risk of Electric Shock


Turn power off before inspection
installation or removal.

Risk of Fire

Keep combustible materials away from lamp.

Unexpected lamp rupture may cause injury, fire, or property damage

Do not use lamp if outer glass is scratched or broken.



Jan 6, 2017 10:57:42 AM For additional information, visit www.gelighting.com