



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## A200/B100 Heater

FH32

UPC:786678629834

### Dimensions:

- Height: X
- Length: X
- Width: X

**Notes:**Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Special Features:** Used with Starter Sizes 0,1, and 2
- **Type:** A200/B100 Heater
- **Design:** NEMA
- **Full Load Current Range:** Ambient 4.08-4.39, 4.72-5.14A, Non-Comp 3.80-4.11, 4.62-4.9A
- **Overload Relay:** Type A and B
- **Trip Type:** Thermal and Fast Trip

### Supporting documents:

- [Eatons Volume 5-Motor Control and Protection](#)
- [Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers](#)
- [Eaton Specification Sheet - FH32](#)

### Certifications:

- UL Listed



- CSA Certified

**Product compliance:** No Data

---

© 2016 Eaton. All rights reserved.