

## F3216/12SMS: 12 - Light Chandelier



### Dimensions:

**Diameter:** 48"      **Overall Height:** 85 3/8"  
**Height:** 32 7/8"      **Wire:** 180" (color/Black)  
**Weight:** 25 lbs.      **Chain:** 60"  
**Mounting Proc.:** Center Lock-Up  
**Connection:** Mounted To Box

### Bulbs:

12 - Candelabra Torpedo 60w Max. 120v - Not included

### Material List:

1 Body - Steel - Smith Steel  
 1 Chain - Steel - Smith Steel

### Safety Listing:

Safety Listed for Damp Locations

### Instruction Sheets:

Trilingual (English, Spanish, and French)  
 (F3213-6\_F3214-8\_F3215-12\_F3216-12\_F3217-20)

**Collection:** Landen

**UPC #:** 014817579208

**Finish:** Smith Steel (SMS)

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	1 1/8			5		

### Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	F3216/12SMS	1	014817579208	51.25	51.25	9.5	14.44	28.7	250	No
NJ Pallet		6		52	40	61.5	74.028	172.2		No
NV Pallet		6		52	40	61.5	74.028	172.2		No