



On Line Catalog



BURNDY Catalog Number	KS20
UPC Number	7818100120000
Description	SERVIT 8 STR - 4 SOL
Status	Active

Web Use  
BURNDY Product Line

	<b>Dimensional</b>
Width (in)	0.51
Size (Hex) or Size (Bolt)	1/2
Cross Flats	0.69
Size (Hex) or Size (Bolt) - in	0.500
B Length (in)	.65
B Length (Fraction)	13/20

	<b>General</b>
Product Description	Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap), Length:1.20

	<b>Conductor(s)</b>
Copper Tap Range	14 AWG-4 AWG
CopperWeld Solid Run Size (Range)	8 AWG-4 AWG
Copper Stranded Run (Range)	8 AWG-4 AWG
CopperWeld Stranded Tap Size (Range)	3#10-8D
Copper Solid Tap (Range)	14 AWG-4 AWG
CopperWeld Solid Tap Size (Range)	#4
Copper Solid Run Size (Range)	8 AWG-4 AWG
CopperWeld Stranded Run Size (Range)	3#10-8D

	<b>Physical</b>
Installation Torque	165
Type of Plating	Unplated
Connector Type	Split Bolt
Plated (Yes or No)	N
Product Material	Copper

	<b>Approvals / Certifications</b>
Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	RUS
Documentation	

For further technical assistance, please contact us

