



On Line Catalog



BURNDY Catalog Number	KSA2
UPC Number	7818100154522
Description	TRITAP SERVIT 2STR-8STR
Status	Active

Web Use
BURNDY Product Line

	Dimensional
Width (in)	0.69
Height (in)	0.78
Size (Hex) or Size (Bolt)	2/3
Cross Flats	0.94
Size (Hex) or Size (Bolt) - in	0.67
B Length (in)	1.24
Bolt Diameter (in)	0.69
Min Tap Size with Max Run Size	#2 Str. (.292) - #8 Sol. (.146)
Max Tap size with Max Run Size	#2 Str. (.292) - #2 Str. (.292)
Min Tap Size with Min Run Size	#6 Sol. (.169) - #8 Str. (.146)
B Length (Fraction)	1-1/4

	General
Product Description	Aluminum Split Bolt, (Run, Tap):: Al-Al: 2 AWG (Str), 2 AWG (Str) , Al-Cu: 6 AWG (Sol), 8 AWG (Str) , Cu-Cu: 2 AWG (Str), 8 AWG (Sol), Tin Plated

	Conductor(s)
Aluminum Run Size (Range)	6 AWG-2 AWG
Copper Tap Range	8 AWG-2 AWG
Copper Stranded Run (Range)	6 AWG-2 AWG
Copper Solid Tap (Range)	8 AWG-2 AWG
Aluminum Tap Size (Range)	8 AWG-2 AWG

	Physical
Installation Torque	275
Type of Plating	Tin
Plated (Yes or No)	Y
Product Material	Aluminum

	Approvals / Certifications
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

