



Double Ended Linear

Double Ended Linear BC300T3Q/CL/TP 120V 6/2PK

High-quality white light with superior lumen performance. Halogen Double Ended lamps provide bright, white light for work lights and security lighting. Rugged construction for busy work sites. Offered in several lengths to meet most application needs. High lumen output provides light where you need it.

Product data

General Information	
Base	R7S [R7s]
Operating Position	Horizontal +/- 4 D [Horizontal +/- 4 D]
Nominal Lifetime (Nom)	2000 h

Light Technical	
Initial lumen (Nom)	5000 lm
Correlated Color Temperature (Nom)	2900 K
Luminous Efficacy (rated) (Nom)	16 lm/W
Color Rendering Index (Nom)	100

Operating and Electrical	
Power (Rated) (Nom)	300 W
Lamp Current (Nom)	2.5 A
Starting Time (Nom)	0.0 s
Voltage (Nom)	120 V

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear (CL)


Approval and Application	
Energy Efficiency Label (EEL)	E

Luminaire Design Requirements	
Bulb Temperature (Max)	900 °C
Pinch Temperature (Max)	350 °C

Product Data	
Order product name	Double Ended Linear BC300T3Q/CL/TP 120V 6/2PK
EAN/UPC - Product	50046677415711
Order code	415711
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	924884936301
Net Weight (Piece)	0.010 kg

Double Ended Linear

Dimensional drawing



Product	D (max)	B (max)	B	B (min)	C (max)
Double Ended Linear	12 mm	115.8 mm	114.2 mm	112.6 mm	117.6 mm
BC300T3Q/CL/TP 120V					
6/2PK					

DESmall 300W R7s 120V T3 CL

