



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

BIPC4/06
 7818101287188
 4/0-6AWG INSUL PRC CONN
 Active

Web Use
 BURNDY Product Line

Width (in)
 Length (in)
 Bolt Size (in)
 Height (in)

Dimensional

2.00
 2.12
 0.31
 2.50

Max Voltage Rating

Electrical

300

Product Description

General

Insulation Piercing Connector, 1/0-4/0 AWG (Run), 6-1/0 AWG (Tap), 300 V

Aluminum Run Size (Range)
 Copper Tap Range
 Copper Stranded Run (Range)
 Aluminum Tap Size (Range)

Conductor(s)

1/0 AWG-4/0 AWG
 6 AWG-1/0
 1/0 -4/0 AWG
 6 AWG-2/0 AWG

Installation Torque
 Type of Plating
 Plated (Yes or No)

Physical

250
 Unplated
 N

UL Listed
 CSA Certified
 Rated for Direct Burial
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Approvals / Certifications

Y
 Y
 N
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175