




14PRR62AGPD: 62" Prairie Fan - Aged Pewter



Specification Images:



Collection: Prairie 62
UPC #:014817576726
Finish: Aged Pewter (AGP)
Blade Finish: Light Grey Weathered Oak
Blade Finish 2: Undefined

Dimensions:

Diameter: 62"
Weight: 25.96 lbs.
Reverse Switch: Remote Controlled
Rev. Switch Location: Remote Transmitter
Motor Size: 125.0 X 25.0
Diameter of Housing: 6.9
Light Kit Included: Yes
Remote Included: Hand Remote
Location of Receiver: Canopy
Remote Group(s):

Bulbs:

1 - LED Integrated Array 15w 120v - included

Features:

- Includes a green, energy-efficient DC motor
- A Finishing Cap is included if the light kit is unnecessary.
- This advanced LED technology is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.
- Remote included for easy operation

Material List:

14 Blade - Wood - Light Grey Weathered Oak
1 Body - Steel - Aged Pewter

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

English (14PRR62XXD-ETL-ENG)
French (14PRR62XXD-ETL-CF)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Lens	Lexan	Frosted White	1				1 1/32	5 1/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	2 3/32			5 1/2		

Blade Details:

Blade Group	Diameter	Included	RPM Hi	CFM Hi	Watts Hi	Amps Hi	RPM Med	CFM Med	Watts Med	Amps Med	RPM Low	CFM Low	Watts Low	Amps Low
	62	Yes	113.0	7233.11	34.24	0.48								

Mounting Options:

Mounting Type	Included	Item	Downrod Length	Downrod Diameter	Overall Height	Blade to Ceiling	Min. Ceiling Height	Canopy Style	Canopy Diameter
Downrod (Included)	yes		6.0	0.5	14.14				5.5

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	14PRR62AGPD	1	014817576726	22	15.25	12	2.33	29	70	Yes
NJ Pallet		30		48	40	76	84.444	870		No
NV Pallet		30		48	40	76	84.444	870		No