


[On Line Catalog](#)
**BURNDY Catalog Number**

BIBS2/04

**UPC Number**

7818102238955

**Description**

2/0-14 ONE SIDED UNITAP,2.84

**Status**

IN L

Active

**Web Use**

BURNDY Product Line

**Dimensional**

Width (in) 1.31  
 Hex Size (Key) 3/16  
 Length (in) 2.86  
 Height (in) 1.38

**Electrical**

Min Voltage Rating 600

**General**

Number of Ports 4  
 Number of Screws 4

**Product Description**

Aluminum Multiple Tap  
 Connector, Clear Insulated, 4 Port,  
 1 Sided Entry, 14-2/0 AWG, Al/Cu  
 Rated

**Conductor(s)**

Aluminum Size (Range) 8 AWG-2/0 AWG  
 Copper Solid Size (Range) N/A  
 Copper Stranded (Range) 14 AWG-2/0 Str

**Physical**

Type of Hardware Aluminum  
 Type of Plating Unplated  
 Insulation Type Plastisol  
 Plated (Yes or No) N  
 Product Material Aluminum

**Approvals / Certifications**

Rated for Direct Burial N  
 UL Listed Y  
 CSA Certified Y  
 ROHS Compatible Compliant  
 UL Recognized N  
 CULUS N  
 Industry Standards UL468A-468B

**Documentation**

**For further technical assistance, please contact us**

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175