


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number

BIBD2/03

7818102239499

Description

2/0-14 TWO SIDED UNITAP,2.19

Status

IN L

Active

Web Use

BURNDY Product Line

Dimensional

Width (in) 1.56
Hex Size (Key) 3/16
Length (in) 2.19
Height (in) 1.38

Electrical

Min Voltage Rating 600

General

Number of Ports 3
Number of Screws 3

Product Description

Aluminum Multiple Tap
Connector, Clear Insulated, 3 Port,
2 Sided Entry, 14-2/0 AWG, Al/Cu
Rated

Conductor(s)

Aluminum Size (Range) 8 AWG-2/0 AWG
Copper Solid Size (Range) N/A
Copper Stranded (Range) 14 AWG-2/0 Str

Physical

Type of Hardware Aluminum
Type of Plating Unplated
Insulation Type Plastisol
Plated (Yes or No) N
Product Material Aluminum

Approvals / Certifications

Rated for Direct Burial N
UL Listed Y
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N
Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175