



Product Number: 49131

Order Abbreviation: QTP2X54T5HOUNVPSNNL

General Description: 2-lamp Universal Voltage electronic ballast for 54W T5HO lamp, packaged 20 pieces per case, without leads

Product Information	
Abbrev. With Packaging Info.	QTP2X54T5HOUNVPSNNL 20/CS 1/SKU
Ballast Factor	1.00
Ballast Height H (in)	0.8660
Ballast Length L (in)	16.6540
Ballast Width W (in)	1.1810
Circuit Type	SERIES
Family Brand Name	QUICKTRONIC Professional
Input Current (Amps)	0.50
Nominal Voltage (V)	120.00
Nominal Voltage (V)	120-277V
Number of Lamps	2
Open Circuit Voltage (V)	<600
Power Factor	>0.98
Primary Lamp Type	FP54T5HO
Sound Rating	A
Starting Method	PROSTART
Starting Temperature - Fahrenheit	-20
Starting Temperature - Celsius	-29
Total Harmonic Distortion (THD)	<10%
Wiring Method	WIRETRAP CONNECTORS
Total Maximum Wattage	121.5



Footnotes

- Data based on primary lamp types. See OSRAM SYLVANIA System Performance Guide for data on other lamp combinations.
- Remote Mounting up to 18 feet
- Complies with FCC 47 CFR Part 18, Non-Consumer
- Minimum starting temperature: -20 F / -29 C