

Rittal – The System.

Faster – better – everywhere.

Wallmounted enclosure – WM 8017.581

Date : Mar 2, 2017

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Wallmounted enclosure – WM 8017.581 - WM363612NC

created: 02.03.2017 build on www.rittal.com/us-en

width

= =

please choose

height

= =

please choose

depth

= =

please choose

material

please choose

protection category

please choose

approvals

please choose



width

= =

please choose

height

= =

please choose

depth

= =

please choose

material

please choose

protection category

please choose

approvals

please choose

Product description

Material:	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish:	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Color:	RAL 7035
Protection category IP to IEC 60 529:	IP 66
Protection category NEMA:	NEMA 4
Supply includes:	Housing with door(s) Left hand hinge Mounting plate Rear wall mounting holes Quarter turn latch with slotted head insert

Product features

Dimensions:	Height: 900 mm (35 ") Width: 900 mm (35 ") Depth: 300 mm (12 ")
Material thickness::	Housing: 2 mm (0.08 ") Door: 2 mm (0.08 ") Mounting plate: 2.5 mm (0.1 ")
Mounting plate:	Height: 870 mm (34 ") Width: 840 mm (33 ")
Packaging unit:	1 pc(s).
Weight/packaging unit:	64 kg (141.1 lb.)
EAN:	83158

Approvals

Approvals:	UL
-------------------	----