



[On Line Catalog](#)



BURNDY Catalog Number
UPC Number
Description
Status

AMS250
 7818102410355
 250-6 DUAL RATED SPLICE
 Active

Web Use
 BURNDY Product Line

Width (in)
 Length (in)
 Hex Size
 H1

Dimensional

1.00
 4.09
 5/16
 1.09

Number of Screws

General

4

Product Description

Aluminum Mechanical Splice, 250
 kcmil-6 AWG, 5/8" Screw Dia, 4
 Screws, 5/16" Hex Size, Al/Cu
 Rated, Tin Plated

Aluminum Size (Range)
 Copper Solid Size (Range)
 Copper Stranded (Range)

Conductor(s)

6 AWG-4/0 AWG
 4 AWG-4/0 AWG
 6 AWG-250 kcmil

Installation Torque
 Type of Plating
 Connector Type
 Plated (Yes or No)
 Product Material

Physical

50
 Tin
 Splice, Reducer
 Y
 Aluminum

Rated for Direct Burial
 UL Listed
 CSA Certified
 ROHS Compatible
 Industry Standards

Approvals / Certifications

N
 Y
 Y
 Exempt
 UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175