



BURNDY Catalog Number
UPC Number
Description
Status

QP10F25X03D
 7818102935777
 FEM DISC-12-10AWG-VINYL
 Active

Web Use
 BURNDY Product Line

Dimensional

Tab Size .250 X .032
 Strip Length 3/8"
 Width (in) 0.29
 Length (in) 0.98
 F - Spacing (in) (Width - Center to Center) 0.13
 B Length (in) 0.25

General

Product Description Brass Female Quick Disconnect, 10-12 AWG, Vinyl Insulated, Tin Plated

Other

Bulk Package QP10F25X03B

Approvals / Certifications

UL Listed N
 CSA Certified N
 ROHS Compatible Compliant
 UL Recognized N
 CULUS Y
 Industry Standards UL467

Conductor(s)

Copper Solid Size (Range) N/A
 Copper Stranded (Range) 12 AWG-10 AWG

Physical

Type of Plating Tin
 Connector Type Female Disconnect
 Insulation Type Vinyl
 Plated (Yes or No) Y

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175