



BURNDY Catalog Number
UPC Number
Description
Status

KLU225
 7818103514133
 2-4/0 CU LUG B
 Active

Web Use
 BURNDY Product Line

Dimensional	
Screw Size	7/16
Length (in)	2.56
Size (Hex) or Size (Bolt)	7/16
Stud Size (in)	5/16
Thickness	0.12
Size (Hex) or Size (Bolt) - in	0.44
B Length (in)	0.77
Pad Width (in)	0.99
N (in)	0.51
Hole Size (in)	0.33
Strip Length	1-5/16
B Length (Fraction)	67/87
General	
Product Description	Copper Terminal, Offset Tongue, 1 Hole, 2-4/0 AWG (Str), 5/16" Stud, 1 Screw
Conductor(s)	
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	2 AWG-4/0 AWG
Physical	
Screw Type	Allen
Installation Torque	204
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Product Material	Copper
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	Y
Industry Standards	UL467
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175