



Color:  Blue

UPC Code: 078477851647

Country Of Origin: Mexico

NEMA:  
5-20R



## 5352-BU

Duplex Receptacle Outlet, Heavy-Duty Industrial Specification Grade, Smooth Face, 20 Amp, 125 Volt, Back or Side Wire, NEMA 5-20R, 2-Pole, 3-Wire, Self-Grounding - Blue

Leviton's line of Extra Heavy-Duty Industrial Grade receptacles are designed and manufactured to withstand the harsh conditions typically associated with industrial environments. Available in a wide variety of configurations, including isolated ground, tamper-resistant, hospital grade, etc., these Industrial Grade devices are the electrical contractor's choice for use in factories, schools, hospitals and commercial office buildings.

### Technical Information

#### AC Horsepower Ratings

**At Rated Voltage:** 1 HP

#### Electrical Specifications

**Amperage:** 20 A

**Dielectric Voltage:** Withstands 3000V min

**Grounding:** Self-Grounding

**Pole:** 2

**Temperature Rise:** Max 30C after 250 cycles OL at 200 percent rated current

**Voltage:** 125 VAC

**Wire:** 3

#### Environmental Specifications

**Flammability:** Rated V-0 per UL 94

**Operating Temperature:** -40°C to 75°C

#### Material Specifications

**Body Material:** PBT Polyester Blend

**Clamp Nuts:** Steel (Galvanized G60)

**Color:** Blue

**Face Material:** PBT Polyester Blend

**Ground Clips:** Brass

**Grounding Screw:** #8 Hex Head, Triple-Drive Brass

**Line Contacts:** 0.030" Phosphor Bronze

**Strap Material:** Galvanized Steel with Riveted Ground Contacts

**Terminal Screws:** #8 Triple-Drive Brass

#### Mechanical Specifications

**Product ID:** Ratings are permanently marked on device

**Terminal Accom.:** #14-#10 AWG

**Terminal ID:** Brass-Hot, Silver-Neutral, Green-Ground

**Termination:** Back and Side Wire

#### Product Features

**Body Material:** PBT Polyester Blend

**Color:** Blue

**Device Type:** Duplex Receptacle Outlet

**Face Material:** PBT Polyester Blend

**Feature 4:** Smooth Face

**Grade:** Heavy-Duty Industrial Specification Grade

**Grounding:** Self-Grounding

**NEMA:** 5-20R

#### Standards and Certifications

**ANSI:** C-73

**CSA C22.2 No. 42:** File 152105

**NEMA:** WD-1 & WD-6

**NOM:** 057

**UL Fed Spec WC-596:** File E13399

**UL498:** File E13399

**Warranty:** 10 Years

### Patents\*

CA2483480


US6743029

MX257790

US8684771

MX321216

\*This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.



Drawing Applies to 15 & 20A Devices

### SPECIFICATION SUBMITTAL

JOB NAME:		CATALOG NUMBERS:	
<input type="text"/>		<input type="text"/>	<input type="text"/>
JOB NUMBER:		<input type="text"/>	<input type="text"/>

**Leviton Manufacturing Co., Inc.**

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday):

+1-800-824-3005

**Leviton Manufacturing of Canada, Ltd.**

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · [www.leviton.com/canada](http://www.leviton.com/canada)

**Leviton S. de R.L. de C.V.**

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · [www.leviton.com.mx](http://www.leviton.com.mx)

Visit our Website at: [www.leviton.com](http://www.leviton.com)

© 2018 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

**Leviton has a global presence.**

If you would like to know where your local Leviton office is located please go to:

[www.leviton.com/international/contacts/](http://www.leviton.com/international/contacts/)

