



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

K4A31U4N  
 7818103704211  
 FOUR:6STR-350 DUAL RATED  
 Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Width (in)	5.04
Length (in)	4.50
Bolt Hole Size (in)	0.56
Thickness	0.31
D - in	3.00
Pad Width (in)	4.72
E - in	1.75
N (in)	0.63
General	
Number of Conductors	4
Product Description	Aluminum Universal Terminal, 4 Conductor, 4 Hole, 6 AWG (Str)-350 kcmil, 1/2" Stud, 1.75" Stud Hole Spacing, 4 Screws, Al/Cu Rated, Tin Plated
Conductor(s)	
Aluminum Size (Range)	6 AWG-350 kcmil
Copper Solid Size (Range)	N/A
Copper Stranded (Range)	6 AWG-350 kcmil
Physical	
Installation Torque	275
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	9/16
Plated (Yes or No)	Y
Product Material	Aluminum
Approvals / Certifications	
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Non-Compliant
Industry Standards	UL467
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175