


[On Line Catalog](#)


BURNDY Catalog Number YA6C2L
UPC Number 7818105018566
Description 6STR CU 2-HOLE SHORT 1/4
Status Active

Web Use
 BURNDY Product Line

Dimensional	
Tongue Angle	Straight
Length (in)	2.01
Barrell Style	Chamfered,Skived
Bolt Hole Size (in)	0.27
Barrel Type	Standard
Thickness	0.08
B Length (in)	0.54
Pad Width (in)	0.45
E - in	0.62
Strip Length	5/8
	General
Number of Holes	2
Product Description	Copper Compression Lug, 2 Hole w/ Inspection Window, 6 AWG, 1/4" Stud, 5/8" Stud Hole Spacing, Short Barrel, Tin Plated
	Conductor(s)
Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	6 AWG
	Physical
Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/4
Color Code	Blue
Plated (Yes or No)	Y
Index Number	7,374
Product Material	Copper
	Approvals / Certifications
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive

BURNDY Technical Services

47 East Industrial Park Drive

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175