


[On Line Catalog](#)


BURNDY Catalog Number YA272N
UPC Number 7818105032499
Description 3/0 CU 2-HOLE LONG 1/2
Status Active

Web Use
 BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	5.01
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.13
B Length (in)	1.50
Pad Width (in)	0.91
E - in	1.75
Strip Length	1-9/16

Number of Holes

General

2
 Copper Compression lug, 2 Hole
 w/o Inspection Window, 3/0 AWG,
 1/2" Stud, 1-3/4" Stud hole
 spacing, Long Barrel, Tin Plated

Product Description

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	3/0 AWG

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Orange
Plated (Yes or No)	Y
Index Number	14
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us