



# Specification Sheet

## C11 Glowescnt Incandescent Lamp (Spun Satin)

Order Number **03025**

### Specifications

Energy Used (Watts).....	40
Domestic Code.....	40C11/GLOWESCENT/CB
Volts.....	120
Brightness (Lumens) .....	320
Average Rated Hours .....	1500
Life (in years)* .....	1.4
Filament Type .....	C7A
Light Center Length (LCL) .....	1 13/16"
Estimated Yearly Energy Cost** .....	\$4.82
Country of Origin.....	China



### Physical Characteristics

Finish .....	White
Base.....	Candelabra
MOL.....	4"

\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/k/Wh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee  
© "Westinghouse" and "You can be sure...if it's Westinghouse" are all registered trademarks of Westinghouse Electric Corporation.

