



**9429-12: AMBIANCE**



**Dimensions:**

**Length:** 5/8"                      **Overall Height:** 1 7/16"  
**Width:** 5/8"  
**Height:** 3/4"

**Bulbs:**

1 - Wedge T3 1/4 5w Max. 12v - Not included

**Material List:**

1 Body - Polycarbonate - Black

**Safety Listing:**

Safety Listed for Dry Locations  
 Safety Listed for Dry Locations  
 Safety Listed for Damp Locations

**Instruction Sheets:**

English (HC-256)

Linear Lighting One Light Lampholder in Black Finish. Minimum Socket Spacing 2

Heat resistant polycarbonate with black finish. Includes landscape clip for outdoor use. 12v only.

Listed for Wet Location for 12V only

**UPC #:**785652942921

**Finish:** Black (12)

**Replacement Bulb Data:**

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
9732									

**Shipping Information:**

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frts. Class	UPS Ship
Individual	9429-12	1	785652942921	0.7	2.7	2.8	0.003	0.01	100	Yes
Master Pack		25	10785652942928	2	6	6	0.042	0.4	100	Yes
Shipping Master		1000	20785652942925	17.25	17.5	15.38	2.687	10	100	Yes
NJ Pallet		2000		48	40	48	53.333	15		No
NV Pallet		2000		48	40	48	53.333	15		No