



Powering Business Worldwide

pe.eaton.com

Eaton General purpose ventilated transformer

V48M28F4516CU

UPC:786680192234

Dimensions:

- **Height:** 36.77 IN
- **Length:** 21.13 IN
- **Width:** 24.88 IN

Weight:369 LB

Notes:10 CFR Part 431 (2016) Efficient

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Special Features:** Fungus-resistant varnished core and coil
- **Type:** Energy-efficient ventilated type DT-3 transformer
- **Coil Material:** Copper
- **Efficiency:** 10 CFR Part 431-2016 (DOE 2016)
- **Enclosure:** NEMA 2
- **Frame:** FR940
- **Frequency Rating:** 60 Hz
- **Insulation:** 220°C
- **Kva Rating:** 45 kVA
- **Material:** Copper windings
- **Mounting:** Floor or wall, upright only
- **Phase:** Three-phase
- **Primary Voltage:** 480 V
- **Secondary Voltage:** 208Y/120 V
- **Sound Level:** NEMA ST-20
- **Tap Size:** 2 at +2.5%, 4 at -2.5%



- **Temperature Rise:** 115 °C rise
- **Voltage Rating:** 480 Vac-208Y/120 Vac

Supporting documents:

- [Eaton Specification Sheet - V48M28F4516CU](#)

Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.