

FEISS

EST. 1955

SF292AF/BS: 4 - Light Indoor Semi-Flush Mount



Dimensions:

Diameter: 16 3/8" **Wire:** 8" (color/Black/White)
Height: 10 1/2" **Connection:** Mounted To Box
Weight: 9.68 lbs.

Bulbs:

4 - Candelabra B Torpedo 60w Max. 120v - Not included

Features:

•

Material List:

1 Body - Steel - Antique Forged Iron / Brushed Steel
 1 Canopy - Steel - Antique Forged Iron / Brushed Steel

Safety Listing:

Safety Listed for Damp Locations / IC
 Safety Listed for Damp Locations / IC

Instruction Sheets:

English (SF292)

Collection: Ethan

UPC #: 014817424089

Finish: Antique Forged Iron / Brushed Steel (AF/BS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Clear	1				5 1/2	13 3/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			3/4	5 1/8		

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	SF292AF/BS	1	014817424089	19	17.18	19	3.589	13.4	250	Yes

Feiss reserves the right to revise the design of components of any product due to parts availability or change in safety listing standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product design that is the sole and exclusive property of Feiss. In compliance with U.S copyright and patent requirements, notification is hereby presented in this form that this literature, or the product it depicts, is not to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Feiss 1/2 A Generation Brands Company.

NJ Pallet		16		48	40	75.5	83.889	214.4		No
NV Pallet		16		48	40	76	84.444	215		No