



Representative

Catalog Number: 664 GP
Product ID: 7TAA003110R0001
UPC Number: 78599101521
Status: Active

Device Plate, Galvanized Steel, GCI Receptacle, For use with Two Gang Recessed Service Floor Box, 90 Cubic Inches, Length 10-1/4 Inches, Width 4-11/16 Inches, Depth 3-3/4 Inches, 3/4 Inch and 1 Inch Conduit Hubs, Cast Iron, Delivers Power, Communications and Data from Standard Conduit with No Exposed Service Fittings and Two Gang Recessed Service Floor Box, 90 Cubic Inches, Length 9-15/16 Inches, Width 5-3/32 Inches, Depth 3-3/4 Inches, 3/4 Inch and 1 Inch Conduit Hubs, Cast Iron, Delivers Power, Communications and Data from Standard Conduit with No Exposed Service Fittings

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121307 Floor boxes
IGCC	4432 Floor boxes
Brand Name	Steel City
Type	Recessed Service
Application	For use with 664 SC and 664 CI floor boxes
Standard	UL E2969
Material	Steel
Knockouts	No

European Specifications (ETIM)

ETIM	EC000006 Cover plate for installation units
Length cover plate	260.35mm
Application	Sub-floor outlet box
Number of single openings	1
Type of fastening	Screwing
With label area	N
Suitable for label area	N
Material	Steel
Colour	Other

Packaging

Inner Quantity	1
Outer Quantity	4
Outer Dimensions (inches)	5.5x5.5x2.8
Weight Uom	28.75 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com