



S28946

100W/LED/HID/TEMP/5K/RC/120V
 100 watt LED Hi-lumen temporary hi-bay caged lamp; 5000K;
 Integrated cord / plug and hook; 120 volts

Features

- Remote control operation
- Retractable handle
- IP64 Rated
- 3 ft. cord with plug
- Outlet for connecting multiple lamps



S28946

Item Number	Product Line	UPC	Input Voltage	Watts	Power Factor	Base	ANSI Base
S28946	Hi-Pro	045923289460	120	100	>0.90	Plug 3-Prong	NEMA 5-15

Lamp Code	Connectable Units	Dimmable/Non-Dimmable	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
100W/LED/HID/TEMP/5K/RC/120V	6 maximum	Non-Dimmable	12"	6-1/4"	10000	50000	5000

Color	CRI	Beam Spread Deg	Pack	Package Type	CEC Status	RoHS Compliant	UL Classification
Natural Light	85	300	4	Box	Lawful for sale in California	Yes	cULus - Listed

Warranty
5 Year Limited



National Toll-Free:
 800.43.SATCO
 (800.437.2826)
www.satco.com

Distribution Centers:
 New York, Florida, Texas,
 Washington, California,
 Puerto Rico

Corporate Offices:
 110 Heartland Blvd.,
 Brentwood, NY 11717
 800.437.2826 631.243.2022
 Fax 631.243.2027

