



59132LE-15: Two Light Ceiling Flush Mount



Dimensions:

Length: 48"
Width: 6 3/4"
Height: 2 1/2"

Connection: Mounted To Box

Bulbs:

2 - Fluorescent Medium Bi-Pin T8 32w Max. 120v - Not included

Features:

- ENERGY STAR® Qualified
- Offers energy saving fluorescent lighting
- Meets Title 24 energy efficiency standards
- Title 24 compliant high efficacy light source that is not required to be listed in the California Energy Commission Appliance database.

Material List:

1 Trim - Steel - White

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (HC-1813FS)

Collection: Drop Lens Fluorescent

Two Light Fluorescent Trim and Chassis with White Trim and Clear Textured Acrylic Diffuser.

Hinged end caps for easy relamping and diffuser security.

Complete Fixture; Reference fixture 59034LE-15

UPC #:785652076657

Finish: White (15)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Acrylic	Clear Textured	1	620248-612	48	6 1/2	2					

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	59132LE-15	1	785652076657	49.25	7.5	3.25	0.695	6.2	100	Yes
NJ Pallet		105		48	40	73.25	81.389	651		No
NV Pallet		90		48	40	73.25	81.389	558		No