



# Specification Sheet

## B10 Torpedo Incandescent Lamp

Order Number **03284**

### Specifications

Energy Used (Watts).....	60
Domestic Code.....	60B10/CB
Volts.....	120
Brightness (Lumens) .....	615
Average Rated Hours .....	1500
Life (in years)* .....	1.4
Filament Type .....	CC2V
Light Center Length (LCL) .....	1 7/8"
Estimated Yearly Energy Cost** .....	\$7.23
Country of Origin.....	China



### Physical Characteristics

Finish .....	Clear
Base.....	Candelabra
MOL.....	3 3/4"

\* Based on 3 hrs./day

\*\* Based on 3 hrs./day 11¢/k/Wh - Cost depends on rates and use.

Specifications are subject to change without notice, please visit [www.westinghouselighting.com](http://www.westinghouselighting.com) for latest information.

Call 1-800-999-2226 or visit [www.westinghouselighting.com](http://www.westinghouselighting.com).

Westinghouse Lighting, Philadelphia, PA 19154-1029, U.S.A. Westinghouse Lighting, a Westinghouse Electric Corporation licensee  
©, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation. Used under license by Westinghouse Lighting. All Rights Reserved.

