

Product Number: 25314

Order Abbreviation: F24T12/D/HO

General Description: 35W, 24" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylight phosphor, 6500K color temperature, 76 CRI



Product Information

Abbrev. With Packaging Info.	F24T12DHO 30/CS 1/SKU
Actual Length (in)	21.909
Actual Length (mm)	556.49
Average Rated Life (hr)	9000
Base	Recessed Double Contact
Bulb	T12
Color Rendering Index (CRI)	76
Color Temperature/CCT (K)	6500
Diameter (in)	1.593
Diameter (mm)	40.46
Industry Standards	ANSI C78.81 - 2001
Initial Lumens at 25C	1400
Mean Lumens at 25C	1134
Mean Lumens at 35C	1134
Nominal Length (in)	24.000
Nominal Length (mm)	609.60
Nominal Wattage (W)	35.00



Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. operating cycles under specified conditions and with ballast meeting ANSI specifications. If operating cycle is increased, there will be a corresponding increase in the average hours life.
- Minimum starting temperature is a function of the ballast; consult the ballast manufacturer.