



84050EN3-185: One Light Outdoor Wall Lantern



Dimensions:

Width:	10"	Extends:	12"
Height:	16 1/4"	Wire:	6 1/2" (color/Black/White)
Weight:	5.2 lbs.	Mounting Proc.:	Cap Nuts
		Connection:	Mounted To Box

Bulbs:

1 - LED Medium A19 9.5w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- LED Bulbs are an efficient, versatile and durable light source that deliver exceptional performance.
- Meets Title 24 energy efficiency standards
- Title 24 compliant when used with included Joint Appendix (JA8) approved lamp.

Material List:

1 Body - Die Cast Aluminum - Undefined

Safety Listing:

Safety Listed for Wet Locations
Safety Listed for Wet Locations

Instruction Sheets:

English (HC-640)
French (F-009)

Collection: Yorktown

One Light LED Outdoor Wall Fixture in Forged Iron Finish with Swirled Marbleized Glass

Forged iron finish in die-cast aluminum with swirled marbleized glass makes a distinctive welcome message.

Design #: D30031

UPC #:785652048050

Finish: Forged Iron (185)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Swirled Marbleize	1									

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	9	5 1/2	1		9	7 1/4

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97502S	Frosted	A19	Medium	9.3	9.3	120v	15000	800 230°	3000	90

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	84050EN3-185	1	785652048050	19.25	14.5	12.25	1.979	6.5	250	Yes
NJ Pallet		36		48	40	77	85.556	234		No
NV Pallet		36		48	40	77	85.556	234		No

